

Specifications

备注 (Remark)

1. 材料 (MATERIAL)

胶芯: PA6T+30%G.F UL94V-0, 颜色: 黑色.

Housing: PA6T+30%G.F UL94V-0, Color: Black

端子: 青铜, 镍底30u"MIN, 表面镀普金

Contact: Bronze, GOLD PLATING OVER ALL

30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 3 AMP

Rated Current: 3 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.




Insulating Resistance: 1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage: AC 500V/Minute.

温度范围: -40° C to +105° C

Temperture Range: -40° C to +105° C



Ordering Information

F185-11 10 A0 B SY A 1

NO.OF PINS
PER ROW
1~40P

Contact Plating

Full Of Gold

Semi-gold

A0=0.8u"

A1=1u"

A2=1.5u"

A3=2u"

A4=3u"

A5=5u"

A6=10u"

A7=15u"

A8=20u"

A9=30u"

S1=Ordinary Tin Plated

S2=Matte Tin Plated

S3=Tin-plated High-temperature

INSULATOR

MATERIAL:

A: PBT

B: PA6T

C: PA9T

D: LCP

PACKING

A: PE Bag

B: Tape & Reel

C: Tube

D: Tube+CAP

E: Tray

RoHS
COMPLIANT

客编: K2976

注意
事项

1. 带*为品质重点检验尺寸

			OPERATION		SCALE		Fit		Yxcon 东莞市宇熙精密连接器有限公司			
			X.X ±0.25		UNIT		MM		www.yxcon.com		Dongguan Yuxi Electronic Co.,Ltd.	
			X.XX ±0.20		SIZE		A4		DESIGN		刘伟 2021.06.23	
			X.XXX ±0.10		SHEET		1/1		CHECK		PART NO.	
A0 2021.06.23 /			新版发行		Angle ±3°						F185-1110A0BSYA1	
REV DATE SYMBOL			MODIFICATION DESCRIPTION		DIM TOL		PROJ.		APPROVE		Customer No.	
											2.54排母8.5mm型高 1*10P 180度 Y型	
											PA6T料 镀普金	
											</	