


Temperture Range: -40°C to $+105^{\circ}\text{C}$

22. 100 plates high temperature



Recommended P. C. B LAYOUT
General Tolerance ± 0.05

1. 带*为品质重点检验尺寸

				OPERATION		SCALE		Fit		Yxcon 东莞市宇熙精密连接器有限公司 Dongguan Yuxi Electronic Co.,Ltd.				
				X.X	±0.25	UNIT		MM						
				X.XX	±0.20	SIZE		A4	DESIGN	李青杰2023.05.04		PART NO.	F136-1203A0CMUB1	
A0	2023.05.04	/		X.XXX	±0.10	SHEET		1/1	CHECK			TITLE:	2.54排母 3.6mm塑高 2*3P SMT; 7.2 U型	
REV	DATE	SYMBOL		Angle	±3°	PROJ.			APPROVE			Customer No.	PA9T材料 镀金麦 麦拉+卷装	
				DIM	TOL									
1			2		3		4		5					