

Ordering Information

F263-12 06 A0 B RY C 1

1. 材料(MATERIAL)

胶芯: PA9T+30%G.F UL94V-0, 颜色: 黑色.

Housing:PA9T+30%G.F UL94V-0,Color:Black

端子: 青銅, 鍍底30μ"MIN, 表面鍍普金

Contact: Bronze, GOLD PLATING OVER ALL

30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 2 AMP

Raring Current:2 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.





Insulating Resistance:1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage:AC 500V/Minute.

温度范围: -40°C to $+105^{\circ}\text{C}$

Temperture Range: -40° C to +105° C



RoHS
COMPLIANT

客编: V1118

注意事项

1. 带*为品质重点检验尺寸

				OPERATION		SCALE		Fit	Yxcon 东莞市宇熙精密连接器有限公司 www.yxcon.com Dongguan Yuxi Electronic Co.,Ltd.			
				X.X	±0.25	UNIT		MM				
				X.XX	±0.20	SIZE	A4	DESIGN	刘伟 2021.03.10	PART NO.	F263-1206A0BRYC1	
				X.XXX	±0.10							
A0	2021.03.10	/	新版发行	Angle	±3°	SHEET	1/1	CHECK	李星宇 3/11	TITLE:	2.0排母6.35mm间距 2*6P 90度 DIP:2.9mm 内径1.1mm Y型 波浪型 PA9T料 镀锡金 V1118	
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	DIM	TOL	PROJ.		APPROVE	李星宇 3/11	Customer No.		

文庫
精密熙宇

