

Specifications

备注 (Remark)

1. 材料 (MATERIAL)

胶芯: PA9T+30%G.F UL94V-0, 颜色: 黑色.

Housing: PA9T+30%G.F UL94V-0, Color: Black

端子: 磷铜, 镍底30u"MIN, 表面镀普金

Contact: Phosphorous, GOLD PLATING OVER ALL

30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 3 AMP

Rating Current: 3 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.





Insulating Resistance: 1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage: AC 500V/Minute.

温度范围: -40° C to +105° C

Temperture Range: -40° C to +105° C



Ordering Information

F136-12 08 A0 C MU B 1

NO. OF PINS
PER ROW
2~40P

Contact Plating

Full Of Gold

A0=0.8u"

A1=1u"

A2=1.5u"

A3=2u"

A4=3u"

A5=5u"

A6=10u"

A7=15u"

A8=20u"

A9=30u"

S1=Ordinary Tin Plated

S2=Matte Tin Plated

S3=Tin-plated High-temperature

Semi-gold

B0=0.8u"

B1=1u"

B2=1.5u"

B3=2u"

B4=3u"

B5=5u"

B6=10u"

B7=15u"

B8=20u"

B9=30u"

INSULATOR

MATERIAL:

B:PA6T

C:PA9T

D:LCP

PACKING

A:PE Bag

B:Tape & Reel

C:Tube

D:Tube+CAP


E:Tray

RoHS
COMPLIANT

客编: V1169

注意
事项

1. 带*为品质重
点检验尺寸



工程部

OPERATION

X.X ±0.25

X.XX ±0.20

X.XXX ±0.10

Angle ±3°

DIM TOL

SCALE

UNIT

SIZE

SHEET

PROJ.

Fit

MM

DESIGN

CHECK

APPROVE

Yxcon

www.yxcon.com

东莞市宇熙精密连接器有限公司

Dongguan Yuxi Electronic Co., Ltd.

A0 2021.08.19 /

新版发行

REV DATE SYMBOL

MODIFICATION DESCRIPTION

李官森 2021.08.19

2021.8.19

2021.8.19

PART NO.

TITLE:

Customer No.

F136-1208A0CMUB1

2.54排母 3.6mm型高 2*8P SMT:7.2 U型 磷铜

塑长: 20.32 PA9T料 镀普金 CAP+卷装600PCS