










REV.	ECN NO.	<u>DESCRIPTION</u>	DATE	DESIGN

卷之三

- 1.材质：LCP+30%GF. UL94V-0 .黑色.
 - 2.产品不可有缩水，起泡，变形，划伤、缺胶、毛刺、刮伤端子等外观不良.
 - 3.未标注C角为CO.15,毛边0.03MM MAX,功能区不可有毛边
 - 4.需实配判定贴板.
 - 5.产品模穴号为沉胶凸字，字体不可高出塑胶面
 - 6.进胶点不能凸出塑胶平面、影响功能性毛边.
 - 7.包装方式：REEL包装



A1	GND	B12	GND			
A2		B11				
A3		B10				
A4	VBUS	B9	WBUS			
A5	CC1	B8	SBU2			
A6	DP1	B7	DN2			
A7	DN1	B6	DP2			
A8	SBU1	B5	CC2			
A9	VBUS	B4	WBUS			
A10		B3				
SUS 301	亮镍40μ”, 48L.					
SHELL SUS 304	亮镍40μ”, 48H.					
Molding	LCP 黑色 C7025 镀金G/F”					
TOLERANCE	NAME(INTENDED USE) CUSTOMER DRAWING	TEYOU Guangzhou TEYOU Precision Dielectric Technology Co.,Ltd.				
X.X	±0.30	X:	±10°	PART NO.		
.XX	±0.20	.X	± 8°	FY23-09TC161F1705-02		
.XXX	±0.10	.XX'	± 5°			
UNITS	mm	DESIGN:	ZXM	DRAWG NO.		
MATERIAL	---	CHED:		FY23-09TC161F1705-02		
FINISH	-----	APPD:				
				SCALE	SHEET	REV.
				1:1	1/2	A

