

Ordering Information

F136-12 12 A0 B MU C 2

备注(Remark)

1. 材料(MATERIAL)

胶芯: PA6T+30%G. F UL94V-0, 颜色: 黑色.

Housing:PA6T+30%G.F UL94V-0, Color:Black

端子: 黄铜, 镍底30u", 表面镀普金

Contact: Brass, GOLD PLATING OVER ALL

30u" NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 3 AMP

Raring Current:3 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.


Insulating Resistance:1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage: AC 500V/Minute.



温度范围: -40°C to $+105^{\circ}\text{C}$

Temperture Range: -40° C to+105° C



Recommended P. C. B LAYOUT

General Tolerance ± 0.05



RoHS
COMPLIANT

客编: K7216

注意事项

1. 带*为品质重点
检验尺寸, 带*为
重点检验尺寸
2. 保持力0.5kgf
Min (公司标准)

				OPERATION		SCALE		Fit		Yyxcon 东莞市宇熙精密连接器有限公司 Dongguan Yuxi Electronic Co.,Ltd.		
				X.X	±0.25	UNIT		MM				
				X.XX	±0.20	SIZE	A4	DESIGN	李官森2024.05.15	PART NO.	F136-1212A0BMUC2	
				X.XXX	±0.10							
A0	2024.05.15	/	新版发行	Angle	±3°	SHEET	1/1	CHECK		TITLE:	2.54排母 3.6mm间距 2*12P SMT 7.2 2型 PA6T料 镀黄金 管装 K7216	
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	DIM	TOL	PROJ.		APPROVE		Customer No.		