

Specifications

备注 (Remark)

1. 材料 (MATERIAL)

胶芯: PA9T+30%G.F UL94V-0, 颜色: 黑色.

Housing: PA9T+30%G.F UL94V-0, Color: Black

端子: 青铜, 镍底30u"MIN, 表面镀普金

Contact: bronze, GOLD PLATING OVER ALL

30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 2 AMP

Rating Current: 2 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.




Insulating Resistance: 1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage: AC 500V/Minute.

温度范围: -40° C to +105° C

Temperture Range: -40° C to +105° C



Ordering Information

F243-12 08 A0 C MU B 1

NO. OF PINS PER ROW 2-40P	Contact Plating Full Of Gold A0=0.8u" A1=1u" A2=1.5u" A3=2u" A4=3u" A5=5u" A6=10u" A7=15u" A8=20u" A9=30u"	Semi-gold B0=0.8u" B1=1u" B2=1.5u" B3=2u" B4=3u" B5=5u" B6=10u" B7=15u" B8=20u" B9=30u"	INSULATOR MATERIAL: B: PA9T C: PA9T D: LCP	PACKING A: PE Bag B: Tape & Reel C: Tube D: Tube+CAP E: Tray
			S1=Ordinary Tin Plated S2=Matte Tin Plated S3=Tin-plated High-temperature	

RoHS
COMPLIANT

客编: K7160

注意
事项

1. 带*为品质重点
检验尺寸

				OPERATION		SCALE		Fit	Yxcon 东莞市宇熙精密连接器有限公司		
				X.X	±0.25	UNIT		MM	www.yxcon.com Dongguan Yuxi Electronic Co.,Ltd.		
A1	2021.08.17	△	更改CAP	X.XX	±0.20	SIZE	A4	DESIGN	李官森2021.08.17	PART NO.	F243-1208A0CMUB1
A0	2021.06.09	/	新版发行	X.XXX	±0.10	SHEET	1/1	CHECK	刘伟 8.17	TITLE:	PH2.0*4.3 2*8P SMT W=4.0 SMT:6.2 PA9T料 镀普金 CAP+800/卷 K7160
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	Angle	±3°	PROJ.		APPROVE	陈嘉杰 8.17	Customer No.	

