

Specifications

备注 (Remark)

1. 材料 (MATERIAL)

胶芯: PA9T+30%G.F UL94V-0, 颜色: 黑色.

Housing: PA9T+30%G.F UL94V-0, Color: Black

端子: 青铜, 镍底30u"MIN, 表面镀金1u"MIN

Contact: Bronze, 1u"MIN GOLD PLATING OVER ALL
30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 2 AMP

Rating Current: 2 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.




Insulating Resistance: 1000 MΩ MIN.

耐电压: AC 500V.

Withstanding Voltage: AC 500V.

温度范围: -40° C to +105° C

Temperature Range: -40° C to +105° C



Ordering Information

F263-12 15 A0 C SY C 2

NO. OF PINS
PER ROW
2-40P

Contact Plating

Full Of Gold

A0=0.8u"

A1=1u"

A2=1.5u"

A3=2u"

A4=3u"

A5=5u"

A6=10u"

A7=15u"

A8=20u"

A9=30u"

S1=Ordinary Tin Plated

S2=Matte Tin Plated

S3=Tin-plated High-temperature

Semi-gold

B0=0.8U"

B1=1U"

B2=1.5U"

B3=2U"

B4=3U"

B5=5U"

B6=10U"

B7=15U"

B8=20U"

B9=30U"

INSULATOR

MATERIAL:

A: PBT

B: PA6T

C: PA9T

D: LCP

PACKING

A: PE Bag

B: Tape & Reel

C: Tube

D: Tube+CAP

E: Tray



客编: K8002

注意: 1. 塑胶供应商W001.

注意事项

OPERATION

X.X	±0.25
X.XX	±0.20
X.XXX	±0.10
Angle	±3°
DIM	TOL

SCALE

Fit

MM

UNIT

SIZE A4

SHEET 1/1

PROJ.

DESIGN

CHECK

APPROVE

Yxcon

东莞市宇熙精密连接器有限公司
Dongguan Yuxi Electronic Co., Ltd.

PART NO.

TITLE:

Customer No.

F263-1215A0CSYC2

2.0排母6.35MM塑高 2*15P 带凸点 (宽3.5 高6.35) Y型
180度 DIP:2.7MM 凹槽式 W=4.0 PA9T料 镀金 K8002

REV

DATE

MODIFICATION DESCRIPTION

CHANGE

APPROVE

2019.5.7

新品发行

杨哲 杨哲