

Specifications

备注(Remark)

1. 材料(MATERIAL)

胶芯: PA6T+30%G.F UL94V-0, 颜色:黑色.

Housing:PA6T+30%G.F UL94V-0,Color:Black

端子: 青铜, 镀底30u"MIN, 表面镀普金

Contact:Bronze, GOLD PLATING OVER ALL

30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 3 AMP

Raring Current:3 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance:20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.

Insulating Resistance:1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage:AC 500V/Minute.

温度范围: -40° C to+105° C

Temperture Range: -40° C to+105° C

Ordering Information

F185-11 XX A0 B SY E 1

NO. OF PINS
PER ROW
1~40P

Contact Plating
Full Of Gold

A0=0.8u"

A1=1u"

A2=1.5u"

A3=2u"

A4=3u"

A5=5u"

A6=10u"

A7=15u"

A8=20u"

A9=30u"

S1=Ordinary Tin Plated

S2=Matte Tin Plated

S3=Tin-plated High-temperature

INSULATOR

MATERIAL:

A:PBT

B:PA6T

C:PA9T

D:LCP




E:PE Bag

B:Tape & Reel

C:Tube

D:Tube+CAP

E:Tray



RoHS
COMPLIANT

注意
事项

1. 带*为品质重点
点检验尺寸

			OPERATION		SCALE		Fit		Yxcon 东莞市宇熙精密连接器有限公司	
			X.X	±0.25	UNIT		MM		www.yxcon.com Dongguan Yuxi Electronic Co.,Ltd.	
			X.XX	±0.20	SIZE		A4		DESIGN	
			X.XXX	±0.10	SHEET		1/1		CHECK	
			Angle	±3°	PROJ.		APPROVE		TITLE:	
			DIM	TOL					Customer No.	
A0	2022.06.02	/	新版发行				李官森 2022.06.02		PART NO.	
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION						F185-11XXA0BSYE1	
									2.54排母8.5mm型高 1*XXP 180度	
									Y型 PA6T料 镀普金	