

Specifications

备注 (Remark)

1. 材料 (MATERIAL)

胶芯: PA6T+30%G. F UL94V-0, 颜色: 黑色.

Housing: PA6T+30%G. F UL94V-0, Color: Black

端子: 青铜, 镍底30u"MIN, 表面镀普金

Contact: Bronze, GOLD PLATING OVER ALL

30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 3 AMP

Rating Current: 3 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.





Insulating Resistance: 1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage: AC 500V/Minute.

温度范围: -40° C to +105° C

Temperture Range: -40° C to +105° C



Ordering Information

F185-11 05 A0 B SY A 1

NO. OF PINS
PER ROW
1-40P

Contact Plating
Full Of Gold

A0=0.8u"

A1=1u"

A2=1.5u"

A3=2u"

A4=3u"

A5=5u"

A6=10u"

A7=15u"

A8=20u"

A9=30u"

S1=Ordinary Tin Plated

S2=Matte Tin Plated

S3=Tin-plated High-temperature

Semi-gold

B0=0.8u"

B1=1u"

B2=1.5u"

B3=2u"

B4=3u"

B5=5u"

B6=10u"

B7=15u"

B8=20u"

B9=30u"

INSULATOR MATERIAL:

A: PBT

B: PA6T

C: PA9T

D: LCP

PACKING

A: PE Bag

B: Tape & Reel

C: Tube

D: Tube+CAP

E: Tray

RoHS
COMPLIANT

客编: K9116

注意
事项

1. 带*为品质重点
检验尺寸

				OPERATION		SCALE		Fit	Yxcon 东莞市宇熙精密连接器有限公司 www.yxcon.com Dongguan Yuxi Electronic Co.,Ltd.				
				X.X	±0.25	UNIT		MM					
				X.XX	±0.20	SIZE	A4	DESIGN	刘伟 2021.06.05	PART NO.	F185-1105A0BSYA1		
A0	2021.06.05	/		X.XXX	±0.10								
REV	DATE	SYMBOL		Angle	±3°	SHEET	1/1	CHECK	李华 2021.06.07	TITLE:	2.54排母8.5mm型高 1*5P 180度 Y型		
				DIM	TOL	PROJ.		APPROVE	李华 2021.06.07	Customer No.	PA6T料 镀普金 600个/盒		
1													

