

备注 (Remark)

1. 材料 (MATERIAL)

胶芯: PA9T+30%G. F UL94V-0, 颜色: 黑色.
Housing: PA9T+30%G. F UL94V-0, Color: Black

端子: 磷铜, 镍底 30u"MIN, 表面镀普金
Contact: Phosphor, 1GOLD PLATING OVER ALL
30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 3 AMP
Rating Current: 3 AMP.

接触阻抗: 20 mΩ MAX.
Contact Resistance: 20 mΩ MAX.




绝缘阻抗: 1000 MΩ MIN.
Insulating Resistance: 1000 MΩ MIN.

耐电压: AC 500V/分钟.
Withstanding Voltage: AC 500V/Minute.

温度范围: -40° C to +105° C
Temperature Range: -40° C to +105° C

F136-12 04 A0 C MU B 4

NO.OF PINS PER ROW	Contact	Plating	INSULATOR	PACKING
2~40P	Full Of Gold	Semi-gold	MATERIAL:	A: PE Bag
	A0=0.8u"	B0=0.8u"	B: PA6T	B: Tape & Reel
	A1=1u"	B1=1U"	C: PA9T	C: Tube
	A2=1.5u"	B2=1.5U"	D: LCP	D: Tube+CAP
	A3=2u"	B3=2U"		E: Tray
	A4=3u"	B4=3U"		
	A5=5u"	B5=5U"		
	A6=10u"	B6=10U"		
	A7=15u"	B7=15U"		
	A8=20u"	B8=20U"		
	A9=30u"	B9=30U"		
	S1=Ordinary Tin Plated			
	S2=Matte Tin Plated			
S3=Tin-plated High-temperature				



RoHS
COMPLIANT

客编: V1169

注意事项

1. 带*为品质重点
检验尺寸
2. 塑胶总长:
10.16

				OPERATION		SCALE		Fit		Yxcon 东莞市宇熙精密连接器有限公司 Dongguan Yuxi Electronic Co.,Ltd.		
				X.X	±0.25	UNIT		MM				
				X.XX	±0.20	SIZE	A4	DESIGN	刘伟 2021.07.09	PART NO.	F136-1204A0CMUB4	
A0	2021.07.09	/	新版发行	X.XXX	±0.10							
				Angle	±3°	SHEET	1/1	CHECK	蔡景平 2021.07.09	TITLE:	FH2.54*3.6 2*4P SMT:7.2 总长10.16 (GRS) U型 镀普金 磷铜 PA9T CAP+卷装/600PCS	
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	DIM	TOL	PROJ.		APPROVE	蔡景平 2021.07.09	Customer No.		

