








REV	DESCRIPTION	DWN	DATE	APPROVEN
R1.0	First issue	Ding	2022.12.06	JIM.KING



A →



Pin Assignment
VIEW A




- Technical specifications:
- Rated voltage/current:
3P 300V/13A
4P 300V/13A
5P 300V/9A
 - Degree of protection: IP67
 - Temperature range: -40°C~+80°C
 - Mating cycles: /500
 - Contact resistance: *5mΩ

4	O-ring	OD14x1.2,SIL,Black	1
3	Pin	Brass; Gold-plated	3~5
2	Housing	TPU,Black	1
1	Nut	Zinc; Nickel plated	1
No.	PART NAME	DESCRIPTION	Q'TY

-TOLERANCES-
UNLESS OTHERWISE
SPECIFIED

UNLESS OTHERWISE SPECIFIED
TOLERANCES FOR MILLIMETERS ARE:
0.5 - 8mm ± 0.20mm
8 - 30mm ± 0.25mm
30 - 120mm ± 0.30mm

dosinconn DOSIN INDUSTRIAL(HK)CO.,LTD
江门市德索连接器有限公司
Jiangmen Dosin Connector Co., LTD
Web: <http://www.dosinconn.com>
Dosin2005@dosinchna.com
Tel:(0086)769-81153906
Fax:(0086)769-81875836



Appr: JIM.KING

Check:

Draw: DING

PART DESCRIPTION:
7/8" female connector, Solder type

P/N: RHT-700-0352

Date	Scale	Unit	Type	Page
2022.12.06	Free	MM	Z	1/1