





[illegible]

B: 2~5P: $\phi 1\text{mm}$
6~17P: $\phi 0.6\text{mm}$



5	O-Ring	Rubber	Black	2
4	Nut M16*1.5	Brass	Nickel	1
3	Body	Brass	Nickel	1
2	Insulator	PA66	Black	1
1	Contacts	Brass	Gold	2~17
NO	Description	Material	Finish	Qty

—TOLERANCES—
UNLESS OTHERWISE
SPECIFIED

UNLESS OTHERWISE SPECIFIED
TOLERANCES FOR MILLIMETERS ARE:
0.5 - 8mm $\pm$ 0.20mm
8 - 30mm $\pm$ 0.25mm
30 - 120mm $\pm$ 0.30mm

dosinconn DOSIN INDUSTRIAL(HK)CO.,LTD
CONNECTOR & CABLE MOUNTING

江门市德索连接器有限公司
Jiangmen Dosin Connector Co., LTD

Web: <http://www.dosinconn.com>
Dosin2005@dosin-china.com
Tel: (0086)769-81153906
Fax: (0086)769-81875836

PART DESCRIPTION:	M12 Female, DIP
-------------------	-----------------

Appr:	JIM. KING
-------	-----------

P/N:	RHT-634-3040
------	--------------

Check:

Date	Scale	Unit	Type	Page
2021.10.09	Free	MM	Z	1/1