





Customer NO:		DOSIN-801-0414		
REV	DESCRIPTION	DWN	DATE	APPROVEN
A	First issue	Mr. CHEN	2017/6/21	John kine
B				



Specifications:

IMPEDANCE: 50 Ohms
Frequency range: 0~6GHZ
VSWR: 1.5MAX
Working voltage: 500V rms @ sea level
Insulation resistance: 5000 Ohms min
Temperature range: -55°C TO +155°C
Relative temperature: $\leq 95\%$ ($40^\circ \text{C} \pm 2^\circ \text{C}$)

NOTE:

Tolerance

X.	± 0.15
X. X	± 0.10
X. XX	± 0.05
Angular	$\pm 5^\circ$

DRAWN
Zelin. CHEN

CHECKED

APPROVALS
John

View



UNIT

MM

SCALE

1:1



Dosin Industrial (H.K.) Co., Ltd

东莞市德索五金电子制品有限公司

Dosin Hardware Electronics Co., Ltd

Name: BNC JACK CONNECTOR

SIZE A Product NO. DOSIN-801-0414

DateTime
2017/6/21

CAD FILE
H/company drawings/BD

SHEET: 1 OF 1

E-mail: dosin2005@163.com
dosin2005@dosin-china.com
Web: http://www.dosinconn.com
TEL: (0086) 769-81153906
FAX: (0086) 769-81875836

DESCRIPTION	MATERIAL	FINISH	QTY
CONTACT PIN	BRASS	GOLD	1
INSULATOR	POM	NONE	1
BODY	BRASS	NICKEL	1