



REV	CONTENT	CHK	DATE
V0.0	CONTENT		2014/08/19

★ A=5.08x(P-1)







PCB LAYOUT  
S=2:1



NOTES:

1. Rating:300V 15A ;
2. Insulation Withstands Voltage: AC2000V/MIN
3. Insulation Resistance: 500MΩ or more at DC500V
4. Using Temperature Range: -40°C~+105°C
5. "★" is the important dimension
6. RoHS compliance



SECTION:A-A

Total Pitch Tolerances in mm										Nominal dimension range in mm										⊥	≡	-	//	
over	over	over	over	over	over	over	over	over	over	over	over	over	over	over	over	over	over	over	over	over	over	over	over	
0	30	53	70	90	115	150	250	350	500	0	30	53	70	90	115	150	200	250	320	0	over	0	100	over
to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	10	all	to	to	150
±0.18	±0.20	±0.25	±0.3	±0.35	±0.44	±0.60	±0.70	±0.85	±0.20	±0.25	±0.30	±0.35	±0.44	±0.55	±0.70	±0.80	±0.90	0.2	0.3	0.3	0.2	0.3	0.5	

ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTE
DWG.	DATE	2014/08/19	SIZE	A4 UNITS mm	SHEET/OF 1/1
CHK.	DATE		SCALE	3:1	2EDG-5.08
APP.	DATE		NAME	F400R-XXP-X	
深圳市金航标电子有限公司		www.kinghelm.com.cn	DWGNO.	02-F400RXXPX	
KH-ZBF4000R-5P-5.08G		0755-83044319			