



Kinghelm®





REV	CONTENT	CHK	DATE
V0.0	CONTENT		2014/08/19

★ A=5.08x(P-1)



NOTES:

1. Rating:300V 15A ;
2. Insulation Withstands Voltage:
AC2000V/MIN
3. Insulation Resistance:
500MΩ or more at DC500V
4. Using Temperature Range: -40°C~+105°C
5. "★" is the important dimension
6. RoHS compliance



A	Total Pitch Tolerances									Nominal dimension range									$\perp$		$\equiv$	$—$ //			
	in mm									in mm															
	over	over	over	over	over	over	over	over	over	over	over	over	over	over	over	over	over	over	over	over	over	over	over	over	over
	0	30	53	70	90	115	150	250	350	500	0	30	53	70	90	115	150	200	250	320	0	10	all	0	100
to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to	to
30	53	70	90	115	150	250	350	500	30	53	70	90	115	150	200	250	320	10	10	all	100	150	100	100	150
± 0.18 ± 0.20 ± 0.25 ± 0.3 ± 0.35 ± 0.44 ± 0.60 ± 0.70 ± 0.85 ± 0.20 ± 0.25 ± 0.30 ± 0.35 ± 0.44 ± 0.55 ± 0.70 ± 0.80 ± 0.90 0.2 0.3 0.3 0.2 0.3 0.5																									

ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTE
DWG.		DATE	2014/08/19	SIZE	A4 UNITS mm SHEET/OF 1/1
CHK.		DATE		SCALE	3:1 2EDG-5.08
APP.		DATE		NAME	F400R-XXP-X
深圳市金航标电子有限公司		www.kinghelm.com.cn			
KH-ZBF4000R-8P-5.08G		0755-83044319		DWGNO. 02-F400RXXPX	