






REV	DESCRIPTION	DWN	DATE	APPROVEN
R1.0	First issue	Ding	2022.12.06	JIM.KING




- Technical specifications:
- Rated voltage/current:
3P 300V/13A
4P 300V/13A
5P 300V/9A
 - Degree of protection:IP67
 - Temperature range:-40°C~+80°C
 - Mating cycles:>500
 - Contact resistance:≤5mΩ

3	Pin	Brass; Gold-plated	3~5
2	Housing	TPU,Black	1
1	Nut	Zinc; Nickel plated	1
No.	PART NAME	DESCRIPTION	Q'TY

-TOLERANCES-
UNLESS OTHERWISE
SPECIFIED

UNLESS OTHERWISE SPECIFIED
TOLERANCES FOR MILLIMETERS ARE:
0.5 - 8mm ± 0.20mm
8 - 30mm ± 0.25mm
30 - 120mm ± 0.30mm

doshconn DOSIN INDUSTRIAL(HK)CO.,LTD
江门市德索连接器有限公司
Jiangmen Dosin Connector Co., LTD
Web: <http://www.dosinconn.com>
Dosin2005@dosin-china.com
Tel: (0086)769-81153906
Fax: (0086)769-81875836



PART DESCRIPTION:
7/8" male connector, Solder type

Appr: JIM.KING

P/N: RHT-700-0351

Check:

Date	Scale	Unit	Type	Page
------	-------	------	------	------

Draw: DING

2022.12.06	Free	MM	Z	1/1
------------	------	----	---	-----