






Product NO.		RHT-634-1353			
ISSUE	DESCRIPTION	DWN	DATE	APPROVEN	
First	First issue	Gavin	2020/07/24	JIM. KING	




Front View



Rear View

Technical specifications:

Rated voltage:	250V AC/DC
Rated current:	4A
Contact resistance:	$\leq 10\text{m}\Omega$
Insulation resistance:	$\geq 100\text{ M}\Omega$
Pollution degree:	3
Degree of protection:	IP67 when
Mating cycles:	≥ 500




5	Contacts	Brass	Gold	4
4	Nut M16*1.5	Brass	Nickel	1
3	O-Ring	Rubber	Black	1
2	Body	Brass	Nickel	1
1	Insulator	PA66	Black	1
NO	Description	Material	Finish	Qty

-TOLERANCES-
UNLESS OTHERWISE
SPECIFIED

UNLESS OTHERWISE SPECIFIED
TOLERANCES FOR MILLIMETERS ARE:
0.5 - 8mm $\pm 0.20\text{mm}$
8 - 30mm $\pm 0.25\text{mm}$
30 - 120mm $\pm 0.30\text{mm}$

dosinconn DOSIN INDUSTRIAL(HK)CO.,LTD
江门市德索连接器有限公司
Jiangmen Dosin Connector Co., LTD
Web: <http://www.dosinconn.com>
Dosin2005@dosin-china.com
Tel: (0086) 769-81153906
Fax: (0086) 769-81875836



PART DESCRIPTION:
M12 4P Male Connector

Appr: JIM. KING

P/N: RHT-634-1353

Check:

Date

Scale

Unit

Type

Page

Draw:

Gavin

2020. 07. 24

Free

MM

Z

1/1