


REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.05.09	

- 规格 Specification:
- 额定值 Rating:3A 125/250VAC
 - 接触电阻 Contact resistance:≤30 mΩ
 - 绝缘电阻 Insulation resistance:≥100 MΩ(DC500V/Min)
 - 电气寿命 Electronics life:>10000 cycles
 - 操作力 Operation force:400±150gf
 - 所有材料符合Rohs要求 All materials are Rohs compliant

PART NO.:


SS-X 03 23 P G-XX N 5 X X
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪

- ① SS: 立式拨柄开关;
② X: A:金属外壳;
BLANK: 塑胶外壳;
③ 03: 额定值3A;
④ 23: 双排三档;
⑤ P: 焊板端子;
⑥ G: 弧形拨柄;
⑦ XX: 拨柄高度H: 3~15mm;
⑧ N: 方形外壳;
⑨ 1: 端子焊脚规格TYPE-1; 2: 端子焊脚规格TYPE-2;
3: 端子焊脚规格TYPE-3; 4: 端子焊脚规格TYPE-4;
5: 端子焊脚规格TYPE-5;
⑩ X: 拨柄颜色: B-黑色; W-白色; R-红色
⑪ X: 主体颜色: B-黑色; W-白色; R-红色



产品字码标识


ANGULAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	桑 葚	VIEW:	MODEL TYPE: SLIDE SWITCH
CHECKED		UNIT: mm/in	PART NO.: SS-0323PG-XXN5XX
APPROVED		SIZE: A4	DWG NO.:

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A0



PCB LAYOUT