







NIC02M-W ASSY




ISO VIEW






SECTION A-A



S/H NIC02P-GN



ISO VIEW



- NOTE -

- 1. BEFORE USING, CHECK THE HARMFUL CRACK, BURR, ETC
- 2. MARKING & CAV.No. BY AS A GENERAL RULE OF KUM
- 3. GENERAL TOLERANCE : SEE BELOW
- 4. ASSY PART

△ 1) TERMINAL

APPLICATION WIRE(SQ)	PART NAME	PART No.
AVSS 0.85~1.25sq	TML NIC-M-M	TK201-00200
AVSS 0.3~0.5sq	TML NIC-M-S	TK201-00100
CHFUS 0.13~0.22sq	TML NIC-M-SS	TK201-00400

- 5. THIS PART IS NON-WATERPROOF CONNECTOR

GENERAL TOLERANCE							
	10MAX	50MAX	100MAX	150MAX	200MAX	200VR	ANGLE
A	±0.2	±0.3	±0.5	±0.8	±1.0	±1.4	±30'

②	S/H NIC02P-GN	HK270-02030	GREEN	PBT
①	NIC02M-W	HK261-02010	WHITE	PBT
NO.	PART NAME	PART No.	COLOR	MATERIAL
	THIRD ANGLE PROJECTION	A	-	JJC
		TOLERANCE	SCALE	JJC
			DESIGN	JJC
			DRAWN	KDK
			CHECKED	CJW
			APPROVED	

CJW	11.03.08	E011-0027	△ A	ADD Applicable Wire	JJC
CJW	10.11.30	-	△ -	RELEASED	JJC
APVD	DATE	NOTE No.	SYM	ALTERATION	DWN

DRAWING NAME	NIC02M-W ASSY
DRAWING No.	HK261-02011-C01A

KUM 케이유엠