





E		F	
DIMENSION(尺寸)			
N0 of conductors(导体数目)	N	YY	
Pitch (间距)	▲P	0.5	±0.05
Span (总间距)	▲SP	0.5*(12-1)	±0.07
Width (宽度)	▲W	0.5*(12+1)	±0.08
Margin (边距)	▲M	0.5	±0.07
	/	/	/
Total length(总长)	▲TL	100	±2.0
Insulator length(绝缘段长)	IL	92	/
Insert Thickness(插接端厚度)	T	0.30	±0.05
Surface Thickness(线身厚度)	ST	0.12	±0.05
Strip length (裸铜长度)	▲S1	4.00	±0.5
	▲S2	4.00	±0.5
Supporting Tape length (补强板长度)	B1	8.00	±1.5
	B2	8.00	±1.5
Strip Slant (线口倾斜)	A1	≤0.3	
Punch Slant (冲孔倾斜)	A2	≤0.3	

Material List (辅料清单)			
NO	ITEM(项目)	SPEC(规格)	QTY(数量)
1			
2			
3			
4			
5			
6			



STRUCTURE (构造)			
NO	ITEM (项目)	SPECIFICATION (规格)	REMARK (备注)
1	INSULATION (胶膜)	Printed 印字 (43mm)	/
		AWM 20624 80C 60V VW-1	
2	SUPPORTING TAPE (补强板)	White 白色 (43mm)	/
		Blue 蓝色 (225mm)	
3	CONDUCTOR 导体	Thickness (厚度)	±0.005
		Width (宽度)	±0.03
		PLATED (电镀)	Sn (40 μ 锡)
4	CONDUCTOR 导体镀层	PLATED (电镀)	/

SHENZHEN MINTRON TECHNOLOGY CO.,LTD.	
品名 (ITEM)	制圖 (DR)
0.5 FFC反向排線-12P TL=100mm	kenny
料号 (DWG.NO)	校對 (CHKD)
MTB-DT12-0100N-4/4/8/8	Thomas
比例 (SCALE)	審核 (APPD)
1:1	Davin
單位 (UNITS)	張數 (SHEET)
mm	1 OF 1
	SIZE
	A4
	REV
	A