



E		F	
DIMENSION (尺寸)			
N0 of conductors (导体数目)		N	YY
Pitch (间距)	▲ P	0.5	±0.05
Span (总间距)	▲ SP	0.5*(12-1)	±0.07
Width (宽度)	▲ W	0.5*(12+1)	±0.08
Margin (边距)	▲ M	0.5	±0.07
	/	/	/
Total length (总长)	▲ TL	50	±2.0
Insulator length (绝缘胶长)	IL	92	/
Insert Thickness (插接端厚度)	T	0.30	±0.05
Surface Thickness (线身厚度)	ST	0.12	±0.05
Strip length (裸铜长度)	▲ S1	3.00	±0.5
	▲ S2	3.00	±0.5
Supporting Tape length (补强板长度)	B1	5.00	±1.5
	B2	5.00	±1.5
Strip Slant (线口斜角)	A1	≤0.3	
Punch Slant (冲孔斜角)	A2	≤0.3	

Material List (辅料清单)		
NO	ITEM(项目)	QTY(数量)
1		
2		
3		
4		
5		
6		



		STRUCTURE (构造)		REMARK (备注)
NO	ITEM (项目)	SPECIFICATION (规格)		
1	INSULATION (胶膜)	Printed 印字 (43um)		/
		AWM 20624 80C 60V VW-1		
2	SUPPORTING TAPE (补强板)	Blue 蓝色 (225um)		/
3	CONDUCTOR 导体	Thickness (厚度)	0. 035	±0. 005
		Width (宽度)	0. 3	±0. 03
4	CONDUCTOR 导体镀层	Plated (电镀)	Sn (40 μ " 锡)	MIN
		Plated (电镀)	/	/

SHENZHEN MINTRON TECHNOLOGY CO.,LTD.		
品名 (ITEM)	制图 (DR)	
0.5 FFC反向排线-12P TL=50mm	kenny	
料号 (PMC NO)	校对 (CHKD)	
MTB-DT12-0050N-3/3.5/5	Thomas	
比例 (SCALE)	审核 (APPD)	
1:1	Dewin	
单位 (UNITS)	张数 (SHEET)	
mm	1 OF 1	
	SIZE	
	A4	
	REV	
	A	

Δ	新图制定	Venn	2024. 9. 13
版次	变更内容	申请人	发行日期

—一般公差 (TOLERANCE)

X. ±.50	.XX ±.10
.X ±.20	.XXX ±.05
ANGLES	±1°