


Technical drawing of a printed circuit board (PCB) showing dimensions A, B, C, D, E, F and a table of dimensions in inches.

The drawing includes a top view of the PCB with dimensions A, B, C, D, E, F. A detailed view of the board shows dimensions W, SP, P, M, S1, and S2. A label '印字面 (Printed)' is shown on the board.

DIMENSION (尺寸)			
	N	YY	
NO of conductors (导体数目)	N	YY	
Pitch (间距)	▲ P	1.0	±0.05
Span (总间距)	▲ SP	1.0*(10-1)	±0.07
Width (宽度)	▲ W	1.0*(10+1)	±0.08
Margin (边距)	▲ M	1.0	±0.10
	/	/	/
Total length (总长)	▲ TL	100	±2.0
Insulator length (绝缘胶长)	IL	92	/
Insert Thickness (插接端厚度)	T	0.30	±0.05
Surface Thickness (线身厚度)	ST	0.12	±0.05
Strip Length (裸铜长度)	▲ S1	4.00	±0.5
	▲ S2	4.00	±0.5
Supporting Tape length (补强板长度)	B1	8.00	±1.5
Strip Slant (线口倾斜)	B2	8.00	±1.5
Punch Slant (冲孔倾斜)	A2	≤0.3	

Material List (辅料清单)			
NO	ITEM(项目)	SPEC(规格)	QTY(数量)
1			
2			
3			
4			
5			
6			



STRUCTURE (构造)				
NO	ITEM (项目)	SPECIFICATION (规格)	REMARK (备注)	
1	INSULATION (胶膜)	Printed 印字 (43um)		
		SP AMM 20624 80C 60V VW-1		
2	SUPPORTING TAPE (补强板)	White 白色 (43um)		
		Blue 蓝色 (225um)		
3	CONDUCTOR 导体	Thickness (厚度)	0.035	±0.005
		Width (宽度)	0.65	±0.03
4	CONDUCTOR 导体镀层	PLATED (电镀)	Sn (40 μ " 锡)	MIN
			/	/



SHENZHEN MINTRON TECHNOLOGY CO.,LTD.									
品名 (TITLE)				制图 (DIB)					
1.0 FFC同向排线-10P TI=100mm				校对 (CHECK)					
料号 (DRAWING NO)				审核 (APPRO)					
MTA-DT10-0100C-4/4/8/8				Davidn					
比例 (SCALE)		1:1		单位 (UNITS)		张数 (SHEET)			
		mm				1 OF 1			
						SIZE		REV	
						A4		A	