





DIMENSION(尺寸)			
NO of conductors(导体数目)	N	YY	
Pitch (间距)	▲ P	0.5	±0.05
Span (总间距)	▲ SP	0.5*(6-1)	±0.07
Width (宽度)	▲ W	0.5*(6+1)	±0.08
Margin (边距)	▲ M	0.5	±0.07
	/	/	/
Total length(总长)	▲ TL	100	±2.0
Insulator length(绝缘胶长)	IL	92	/
Insert Thickness(插接端厚度)	T	0.30	±0.05
Suface Thickness(线身厚度)	ST	0.12	±0.05
	Strip length (裸铜长度)	▲ S1	4.00
Supporting Tape length (补强板长度)	▲ S2	4.00	±0.5
	B1	8.00	±1.5
	B2	8.00	±1.5
Strip Slant (线口倾斜)	A1	≤0.3	
Punch Slant (冲孔倾斜)	A2	≤0.3	

Material List (辅料清单)			
NO	ITEM(项目)	SPEC(规格)	QTY(数量)
1			
2			
3			
4			
5			
6			



STRUCTURE (构造)			
NO	ITEM (项目)	SPECIFICATION (规格)	REMARK (备注)
1	INSULATION (胶膜)	Printed 印字 (43um)	
		AWM 20624 80C 60V W-1	/
2	SUPPORTING TAPE (补强版)	Blue 蓝色 (225um)	/
3	CONDUCTOR 导体	Thickness (厚度)	0.035
		Width (宽度)	0.3
4	CONDUCTOR 导体镀层	Plated (电镀)	Sn (40 μ " 锡)
			/

Δ	新图制定	Venn	2024. 9. 13	一般公差 (TOLERANCE)		MTB-DT06-0100N-4/4/8/8	审核 (APPD)	Dawin
				X ± .50 X ± .20 ANGLES ±1°	.XX ± .10 .XX ± .05			
版本	变更内容	申请人	发行日期	比例 (SCALE)	单位 (UNITS)	张数 (SHEET)	SIZE	REV
				1:1	mm	1 OF 1	A4	A