






DIMENSION(尺寸)			
No of conductors(导体数目)	N	YY	
Pitch (间距)	▲ P	0.5	±0.05
Span (总间距)	▲ SP	0.5*(50-1)	±0.07
Width (宽度)	▲ W	0.5*(50+1)	±0.08
Margin (边距)	▲ M	0.5	±0.07
	/	/	/
Total length(总长)	▲ TL	100	±2.0
Insulator length(绝缘胶长)	IL	92	/
Insert Thickness(插接端厚度)	T	0.30	±0.05
Surface Thickness(线身厚度)	ST	0.12	±0.05
Strip length (裸铜长度)	▲ S1	4.00	±0.5
	▲ S2	4.00	±0.5
Supporting Tape length (补强板长度)	B1	8.00	±1.5
	B2	8.00	±1.5
Strip Slant (线口倾斜)	A1	≤0.3	
Punch Slant (冲孔倾斜)	A2	≤0.3	



Material List (辅料清单)			
NO	ITEM (项目)	SPEC (规格)	QTY (数量)
1			
2			
3			
4			
5			
6			

STRUCTURE (构造)				
NO	ITEM(项目)	SPECIFICATION (规格)		REMARK (备注)
		Printed 印字 (43um)		
1	INSULATION (胶膜)	AWM 20624 80C 60V VW-1	/	
		White 白色 (43um)		
2	SUPPORTING TAPE (补强板)	Blue 蓝色 (223um)	/	
3	CONDUCTOR 导体	Thickness (厚度)	0.035	±0.005
		Width (宽度)	0.3	±0.03
4	CONDUCTOR 导体	PLATED (电镀)	Sn (40 μ " 锡)	MIN
		PLATED (电镀)	/	/



品名 (TITLE)		制图 (DR)	
0.5 FFC同向排线-50P TL=100mm		Kennly	
料号 (DRAWING NO)		校对 (CHECK)	
MTA-DT50-0100N-4/4/8/8		Thomas	
比例 (SCALE)		审核 (APPD)	
1:1		Dewin	
单位 (UNITS)	张数 (SHEET)	尺寸 (SIZE)	备注 (REMARK)
mm	1 OF 1	A4	A
			