



SCHMATIC



VIEW K

ELECTRICAL RATING: 0.5A 24V DC ; 0.2A 48V DC  
 CONTACT RESISTANCE: 100mΩ MAX  
 INSULATION RESISTANCE: 100MΩ MIN. 500V DC  
 DIELECTRIC STRENGTH: 500V AC FOR 1 MINUTE  
 OPERATING FORCE: 350±150gf  
 OPERATING LIFE: 10000 cycles  
 OPERATING TEMPERATURE RANGE: -20°C ~ +70°C

MODEL NO.	TRAVEL	NUMBER OF POSITIONS
RS-02	45°	①,②
RS-03	90°	①,②,③
RS-04	135°	①,②,③,④
RS-05	180°	①,②,③,④,⑤
RS-06	225°	①,②,③,④,⑤,⑥
RS-07	270°	①,②,③,④,⑤,⑥,⑦
RS-08	315°	①,②,③,④,⑤,⑥,⑦,⑧



P.C.B LAYOUT  
BOTTOM VIEW

电话 : 0769-82310511-867  
 邮箱 : hooya89@hooya.hk  
 V : hooya89

				TOLERANCE UNLESS SPECIFIED							
7	SPRING	STEEL WIRE	1	NATURAL	UP TO 5mm: ±0.1	ANGULAR					
6	CONTACT	BRASS STRIP	1	Au PLATED	ABOVE 5mm: ±0.2	±1°					
5	TERMINAL B	BRASS STRIP	1	Au PLATED			NO	DATE	REVISIONS		BY APPD
4	TERMINAL A	COPPER STRIP	7	Au PLATED	TITLE : ROTARY SWITCH		UNIT : MM	ROHS COMPLIANT	DWN		
3	CASE	LCP	1	BLACK	MODEL: RS-04		SCALE: 1:1		CHK'D		
2	COVER	PA66	1	BLACK					APPD		
1	KNOB	PA66	1	BLACK							
NO.	PART NAME	MATERIAL	QTY	FINISHING	DONGGUANG HAOYU ELECTRONICS CO., LTD 东莞市弘皓电子有限公司				PRO.AGL:		REV :A0