





NOTES:

1. 额定值 RATING: 16A 125/250VAC 40T125 (UL,CUL; ENEC17; N; CQC)
16(6)A 125/250VAC 40T125 (UL,CUL; ENEC17; N; CQC)
16A 42VDC 40T125 (UL,CUL; ENEC17; N; CQC)
2. 功能 FUNCTIONAL: 见电路图 SEE CIRCUIT DESCRIPTION
3. 接触电阻 CONTACT RESISTANCE: <50mΩ
4. 绝缘电阻 INSULATION RESISTANCE: >100MΩ (500VDC BETWEEN OPEN CONTACTS)
5. 耐电压 DIELECTRIC STRENGTH: >1500VAC 0.5mA 1 MINUTE



5	→	10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN LMC 2020.08.24	ALL SIZE ARE IN	MM		
4	→	9	→	RANGE	TOLERANCE					SCALE	NO		
3	→	8	→	X	±0.30					MAT'L	***		
2	→	7	→	X.X	±0.20					MATERIAL NO.		DRAWING NO.	REV.
1	→	6	→	X.XX	±0.10					FR04-201B3Q16L-R		*****	A0
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1'	LEGION ELECTRONIC & HARDWARE CO., LTD.							