



1. 额定值 RATING: 16A 125/250VAC 40T125 (UL, C-UL; ENEC17; N; CQC)  
16(6)A 125/250VAC 40T125 (UL, C-UL; ENEC17; N; CQC)  
16A 42VDC 40T125 (UL, C-UL; ENEC17; N; CQC)
2. 功能 FUNCTIONAL: 见电路图 SEE CIRCUIT DESCRIPTION
3. 接触电阻 CONTACT RESISTANCE:  $<50\text{m}\Omega$
4. 绝缘电阻 INSULATION RESISTANCE:  $>100\text{M}\Omega$  (500VDC BETWEEN OPEN CONTACTS)
5. 耐电压 DIELECTRIC STRENGTH:  $>1500\text{VAC}$  0.5mA 1 MINUTE



|              |             |               |             |                        |           |                                        |         |        |                                |                  |       |                                                                                       |      |
|--------------|-------------|---------------|-------------|------------------------|-----------|----------------------------------------|---------|--------|--------------------------------|------------------|-------|---------------------------------------------------------------------------------------|------|
| <div>5</div> | →           | <div>10</div> | →           | DIMENSIONAL TOLERANCES |           | APPROVED                               | CHECKED | DESIGN | DRAWN<br><br>LMC<br>2020.08.25 | ALL SIZE ARE IN  | MM    |  |      |
| <div>4</div> | →           | <div>9</div>  | →           | RANGE                  | TOLERANCE |                                        |         |        |                                | SCALE            | NO    |                                                                                       |      |
| <div>3</div> | →           | <div>8</div>  | →           | X                      | ±0.30     |                                        |         |        |                                | MAT'L            | ***   |                                                                                       |      |
| <div>2</div> | →           | <div>7</div>  | →           | X.X                    | ±0.20     |                                        |         |        |                                | MATERIAL NO.     |       | DRAWING NO.                                                                           | REV. |
| <div>1</div> | →           | <div>6</div>  | →           | X.XX                   | ±0.10     |                                        |         |        |                                |                  |       |                                                                                       |      |
| NO           | DESCRIPTION | NO            | DESCRIPTION | ANGLES                 | ±1'       | LEGION ELECTRONIC & HARDWARE CO., LTD. |         |        |                                | FR04-302B3Q16L-R | ***** | AO                                                                                    |      |