

4



3

2

1

D

D






PCB. LAYOUT

NOTES:

1. Rating: 6A 125/250VAC (UL; CUL)
6A 42VDC (UL; CUL)
2. Contact resistance: <50mΩ
3. Insulation resistance: >100MΩ
(500VDC between open contacts)
4. Dielectric strength: >1500V 1 minute
5. Color: cover is black, body is black.
button is black

C

C



③

B

品 名	柄高X. X
VS14-C24DBD06-A03	3.0
VS14-C24DBD06-A06	6.0
VS14-C24DBD06-A08	8.0
VS14-C24DBD06-A10	10.0
VS14-C24DBD06-A12	12.0

B

A

A

5	4	3	2	1
⑤	→	⑩	→	DIMENSIONAL TOLERANCES
④	→	⑨	→	RANGE TOLERANCE
③	→	⑧	→	X ±0.30
②	→	⑦	→	X.X ±0.20
①	→	⑥	→	X.XX ±0.10
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES ±1°
LEGION ELECTRONIC & HARDWARE CO., LTD.				
APPROVED CHECKED DESIGN DRAWN LMC 2023.07.03				
ALL SIZE ARE IN MM				
SCALE NO				
MAT'L ***				
MATERIAL NO.				
VS14-C24DBD06-A**				
DRAWING NO. REV.				
***** A0				

4

3

2

1