

4



3

2

1

D

D






PCB. LAYOUT

NOTES:

1. Rating: 6A 125/250VAC (UL; CUL)
6A 42VDC (UL; CUL)
2. Contact resistance: <50mΩ
3. Insulation resistance: >100MΩ
(500VDC between open contacts)
4. Dielectric strength: >1500V 1 minute
5. Color: cover is black, body is black.
button is black

C

C



③

B

品 名	柄高X. X
VS14-C25DBD06-A03	3.0
VS14-C25DBD06-A06	6.0
VS14-C25DBD06-A08	8.0
VS14-C25DBD06-A10	10.0
VS14-C25DBD06-A12	12.0

B

A

A

⑤	→	⑩	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM		
④	→	⑨	→	RANGE	TOLERANCE				LMC	SCALE	NO		
③	→	⑧	→	X	±0.30				2023.07.03	MAT'L	***		
②	→	⑦	→	X.X	±0.20					MATERIAL NO.		DRAWING NO.	REV.
①	→	⑥	→	X.XX	±0.10					VS14-C25DBD06-A**		*****	A0
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1'	LEGION ELECTRONIC & HARDWARE CO., LTD.							

4

3

2

1