




REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

技术要求Specification:

1. 材质Material: PA66 UL94V-0:
2. 额定电流 Current rating:1.0A AC,DC
3. 额定电压 Voltage rating: 50V AC,DC
4. 温度范围 Temperature range:-25℃to+85℃
5. 接触电阻 Contact resistance:<30mΩ
6. 绝缘电阻Insulation resistance:>100MΩ
7. 耐压Withstand voltage:500V AC/minute
8. 塑件表面平整光洁, 无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。

Plastic surface smooth and clean, no obvious burrsbubbles, distortion, gate strain, lack of material and otherundesirable phenomena.

Part No	Pin	A	B	C	D
C125E11-Y2P11	2	1.25	2.00	3.75	6.25
C125E11-Y3P11	3	2.50	3.20	5.00	
C125E11-Y4P11	4	3.75	4.30	6.25	
C125E11-Y5P11	5	5.00	4.30	7.50	8.75
C125E11-Y6P11	6	6.25	6.25	8.75	8.75
C125E11-Y7P11	7	7.50	6.25	10.00	8.75
C125E11-Y8P11	8	8.75	6.25	11.25	8.75
C125E11-Y9P11	9	10.00	6.25	12.50	8.75
C125E11-Y10P11	10	11.25	8.30	13.75	10.70
C125E11-Y11P11	11	12.50	8.30	15.00	10.70
C125E11-Y12P11	12	13.75	8.30	16.25	10.70
C125E11-Y13P11	13	15.00	8.30	17.50	10.70
C125E11-Y14P11	14	16.25	8.30	18.75	10.70
C125E11-Y15P11	15	17.50	8.30	20.00	10.70
C125E11-Y16P11	16	18.75	8.30	21.25	

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X ±0.30	X.* ±1*	PART NO. C125E11-YXP11	TITLE: GH1.25MM HOUSING		
.XX ±0.20			MANUFACTURE DWG		
.XXX ±0.10					
UNITS	mm	DESIGN: Ethan			
MATERILA	— — —	CHED: Olvia		SCALE	SHEET
FINISH	— — —	APPD: Ava		N:A	1/1