






REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



技术要求 Specification:

1、材质:磷青,表面镀锡,

Material:Phos.Bronze Tin-Plated

镀层:Sn>2.50um, Ni>0.50um

2、零件外观不得有有害毛刺、尖角、锐边和机械损伤:表面镀层应均匀、光亮、无雾斑、剥层等缺陷;


Parts may not have the appearance of harmful burrs,sharp corners,sharp edges and mechanical damage,surface coating should be uniform, bright,no fog spots,delamination and other defects defects.

3.适用线号:AWG#32-#28

Wirerange: AWG#32-#28

3、适用线号:AWG#32-#28:

Wirerange: AWG#32-#28

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X ±0.20	X.* ±10°	PART NO.	TITLE:		
.XX ±0.10	.X* ± 8°	B1251-2DP1	GH1.25MM TERMINAL		
.XXX ±0.05	.XX* ± 5°	DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia		SCALE	SHEET
MATERILA	— — —	APPD: Ava		N:A	1/1