




- NOTES-
1. MATERIAL SEE TABLE;
 2. ELECTRICAL PERFORMANCES:
 - 2-1. RATED CURRENT: 0.3A;
 - 2-2. CONTACT RESISTANCE: 90mΩ Max. with AC 20mV, 1kHz and 1mA;
 - 2-3. INSULATION RESISTANCE: 50mΩ min. With DC 100V;
 3. MECHANICAL PERFORMANCES:
 - 3-1. DURABILITY: 30 CYCLES;
 - 3-2. OPERATION TEMPERATURE: -40℃ To +85℃;

ASSEMBLY



Ordering Information

HC-PBB40C - NDS - 0.4V - ** - 02

No. of Pins	Nature DS=Female	PITCH	High (H)
10~120Pin	0.4V=0.4mm	1.5~1.50mm	2.0~2.00mm
12=12Pin		2.5~2.50mm	3.0~3.00mm
.....		3.5~3.50mm	4.0~4.00mm

Pin	10	12	20	24	30	34	40	44	50	60	70	80	90	100	120
A	4.60	5.00	6.60	7.40	8.60	9.40	10.60	11.40	12.60	14.60	16.60	18.60	20.60	22.60	26.60
B	-	-	1.93	2.43	3.18	3.68	5.08	5.86	5.50	6.00	7.00	8.00	9.00	10.00	14.00
C	1.60	2.00	3.60	4.40	5.60	6.40	7.60	8.40	9.60	11.60	13.60	15.60	17.60	19.60	23.60
D	1.00	1.00	1.00	1.20	1.50	2.30	3.20	3.20	3.20	3.20	3.20	3.20	3.20	3.20	3.20

2	Housing	1	LCP	Glass:30%	Black
1	Terminal	N	C5240ESH	Ni 50~90u"UNDERPLATING, GOLD FLASH OVER ALL	
ITEM	Part Name	Q'TY	MATERIAL	MATERIAL	REMARK

			GENERAL TOLERANCE		制 图 DRAWING	 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD				
			DIM	TOL	审 核 CHECK					
			X. X	±0.30	批 准 APPROVAL	产 品 名 称 TITLE	0.4 双槽 贴片 母座 (BTB)	版 本 REV.	A	
			X. XX	±0.20		产 品 料 号 PART NO.	HC-PBB40C-NDS-0.4V-XX-02	单 位 UNITS	mm	
1	初版发行		X. XXX	±0.10	比 例 SCALE					
序号 No.	变更内容 MODIFY CONTENT	日 期 MODIFY DATE	Angle	±3.0°	投 影 Projection		材 料 MATERIAL		页 次 SHEET	1/1