









REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 2.5
- 2.Voltage Rating: 250V AC DC
- 3.Current Rating: 3A AC DC
- 4.Insulation Resistance: 800MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 1000V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃

Part No	Pin	A	B	C
D254E1L1-2W2P43	2	2.50	10.00	7.50
D254E1L1-2W3P43	3	5.00	12.50	10.00
D254E1L1-2W4P43	4	7.50	15.00	12.50
D254E1L1-2W5P43	5	10.00	17.50	15.00
D254E1L1-2W6P43	6	12.50	20.00	17.50
D254E1L1-2W7P43	7	15.00	22.50	20.00
D254E1L1-2W8P43	8	17.50	25.00	22.50
D254E1L1-2W9P43	9	20.00	27.50	25.00
D254E1L1-2W10P43	10	22.50	30.00	27.50
D254E1L1-2W11P43	11	25.00	32.50	30.00
D254E1L1-2W12P43	12	27.50	35.00	32.50
D254E1L1-2W13P43	13	30.00	37.50	35.00
D254E1L1-2W14P43	14	32.50	40.00	37.50
D254E1L1-2W15P43	15	35.00	42.50	40.00
D254E1L1-2W16P43	16	37.50	45.00	42.50

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.X ±0.30	X.* ±5°	PART NO. D254E1L1-2WXP43	TITLE: WAFER XHB2.54 立贴带扣	
.XX ±0.20	X.X* ±3°		MANUFACTURE DWG	
.XXX ±0.10	X.XX* ±1°			
UNITS	mm	DESIGN: Ethan		
MATERILA	— — —	CHED: Olvia		
FINISH	— — —	APPD: Ava		
			SCALE N:A	SHEET 1/1