


REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



技术要求:

1. 标识清晰可见, 表面不得有划痕, 裂纹, 变形, 起泡污损, 毛刺等明显影响使用功能和接触性能的缺陷;
2. 材料: 磷铜, 厚度0.2mm;
3. 表面处理: 镀锡;
4. 额定功率: 250V AC/DC 3A;
5. 温度范围: -25~+85C;
6. 接触电阻: ≤0.22Ω;
7. 绝缘电阻: ≥500MΩ;
8. 耐压: 1000V AC/Min;
9. 适用线规: WAG28#~22#.

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd				
X.X ±0.30	X.* ±5°	PART NO. B3961-2DP1		TITLE: VH3.96 端子		
.XX ±0.20	X.X* ±1°					
.XXX ±0.10	X.XX* ±0.5°	DESIGN: Ethan		MANUFACTURE DWG		
UNITS	mm					
MATERILA	— — —	CHED: Olvia			SCALE	SHEET
FINISH	— — —	APPD: Ava			N:A	1/1