



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 1.25
- 2.Voltage Rating: 125V AC DC
- 3.Current Rating: 1A AC,DC
- 4.Insulation Resistance: 100MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 500V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃

Part No	Pin	A	B	C
D125E1W1-2W2P43	2	1.25	5.75	3.75
D125E1W1-2W3P43	3	2.50	7.00	5.00
D125E1W1-2W4P43	4	3.75	8.25	6.25
D125E1W1-2W5P43	5	5.00	9.50	7.50
D125E1W1-2W6P43	6	6.25	10.75	8.75
D125E1W1-2W7P43	7	7.50	12.00	10.00
D125E1W1-2W8P43	8	8.75	13.25	11.25
D125E1W1-2W9P43	9	10.00	14.50	12.50
D125E1W1-2W10P43	10	11.25	15.75	13.75
D125E1W1-2W11P43	11	12.50	17.00	15.00
D125E1W1-2W12P43	12	13.75	18.25	16.25
D125E1W1-2W13P43	13	15.00	19.50	17.50
D125E1W1-2W14P43	14	16.25	20.75	18.75
D125E1W1-2W15P43	15	17.50	22.00	20.00
D125E1W1-2W16P43	16	18.75	23.25	21.25

TOLERANCE				 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X	±0.30	X.*	±5°	PART NO. D125E1W1-2WXP43	TITLE: WAFA GH1.25 贴片带扣		
.XX	±0.20	X.X*	±3°				
.XXX	±0.10	X.XX*	±1°				
UNITS		mm		DESIGN:	Ethan		
MATERILA		— — —		CHED:	Olvia		
FINISH		— — —		APPD:	Ava		
						SCALE N:A	SHEET 1/1

