







NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 1.5
- 2.Voltage Rating: 250V AC DC
- 3.Current Rating: 1A AC DC
- 4.Insulation Resistance: 500MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 500V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃

Part No	Pin	A	B	C
D150F1W1-2W2P43	2	1.50	6.00	3.65
D150F1W1-2W3P43	3	3.00	7.50	5.15
D150F1W1-2W4P43	4	4.50	9.00	6.65
D150F1W1-2W5P43	5	6.00	10.50	8.15
D150F1W1-2W6P43	6	7.50	12.00	9.65
D150F1W1-2W7P43	7	9.00	13.50	11.15
D150F1W1-2W8P43	8	10.50	15.00	12.65
D150F1W1-2W9P43	9	12.00	16.50	14.15
D150F1W1-2W10P43	10	13.50	18.00	15.65
D150F1W1-2W11P43	11	15.00	19.50	17.15
D150F1W1-2W12P43	12	16.50	21.00	18.65
D150F1W1-2W13P43	13	18.00	22.50	20.15
D150F1W1-2W14P43	14	19.50	24.00	21.65
D150F1W1-2W15P43	15	21.00	25.50	23.15
D150F1W1-2W16P43	16	22.50	27.00	24.65

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.X ±0.30	X.* ±5°	PART NO. D150F1W1-2WXP43	TITLE: WAFER 1.50 贴片	
.XX ±0.20	X.X* ±3°			
.XXX ±0.10	X.XX* ±1°			
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG	
MATERILA	— — —	CHED: Olvia		
FINISH	— — —	APPD: Ava		
			SCALE N:A	SHEET 1/1