


REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

Specification:


1,Material: Phos.Bronze Tin-Plated
Coating: Sn>80u”,

2,Applicable wire: AWG#30-#24


4.The appearance of the parts shall not have harmful burrs, sharp corners, sharp edges and mechanical damage: the surface plating should be uniform and bright, without fog spots, peeling and other defects;




料带图 比率: 1:2



SECTION A-A



SECTION B-B



SECTION C-C

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X ±0.20	X.* ±10°	PART NO. B2001-2DP1		TITLE: 2.0 Pitch	
.XX ±0.10	.X* ± 8°				
.XXX ±0.05	.XX* ± 5°			DESIGN: Ethan	
UNITS	mm	CHED: Olvia			
MATERILA	— — —	APPD: Ava		 SCALE SHEET	
FINISH	— — —			N:A 1/1	