

1


2

3

4

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.05.09	

16.20 [0.638]



10.50 [0.413]

规格 Specification:

1.额定值 Rating:3A 125/250VAC

2.接触电阻 Contact resistance:≤30 mΩ

3.绝缘电阻 Insulation resistance:≥100 MΩ(DC500V/Min)

4.电气寿命 Electronics life:>10000 cycles

5.操作力 Operation force:500±150gf

6.所有材料符合Rohs要求 All materials are Rohs compliant

PART NO.:

SS-X 03 12 S G-XX N 2 X X
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪

① SS: 立式拨柄开关;

② X: A: 金属外壳;

BLANK: 塑胶外壳;

③ 03: 额定值3A;

④ 12: 单排两档;

⑤ S: 焊线端子;

⑥ G: 弧形拨柄;

⑦ XX: 拨柄高度H: 3~15mm;

⑧ N: 方形外壳;

⑨ 1: 端子焊脚规格TYPE-1; 2: 端子焊脚规格TYPE-2;

3: 端子焊脚规格TYPE-3; 4: 端子焊脚规格TYPE-4;

5: 端子焊脚规格TYPE-5;

⑩ X: 拨柄颜色: B-黑色; W-白色; R-红色

⑪ X: 主体颜色: B-黑色; W-白色; R-红色

A

A

B

B

C

C

D


D

5.50 [0.217]

4.00 [0.157] Travel

3.30 [0.130]

产品凸码标识



8.50 [0.335]

2.00 [0.079]

4.50 [0.177]


9.00 [0.354]

0.50 [0.020]


4.00 [0.157]

XKLB C **RU** USSS Series
3A 125/250VAC

产品字码标识



CIRCUIT



ANGULAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	

XKLB

DESIGN

桑 葚

VIEW:

MODEL TYPE:
SLIDE SWITCH

CHECKED

UNIT: mm/in

PART NO.:
SS-0312SG-XXN2BB

APPROVED

SIZE: A4

DWG NO.:

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A0

1

2

3

4

www.helloxkb.com

www.helloxkb.cn

www.xk-dg.cn