

1


2

3

4

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.05.09	

16.20 [0.638]



10.50 [0.413]

规格 Specification:

- 1.额定值 Rating:3A 125/250VAC
- 2.接触电阻 Contact resistance: $\leq 30\text{ m}\Omega$
- 3.绝缘电阻 Insulation resistance: $\geq 100\text{ M}\Omega$ (DC500V/Min)
- 4.电气寿命 Electronics life: > 10000 cycles
- 5.操作力 Operation force: $500\pm 150\text{ gf}$
- 6.所有材料符合Rohs要求 All materials are Rohs compliant

PART NO.:


SS-X 03 12 S G-XX N 2 X X
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪

- ① SS: 立式拨柄开关;
② X: A: 金属外壳;
BLANK: 塑胶外壳;
③ 03: 额定值3A;
④ 12: 单排两档;
⑤ S: 焊线端子;
⑥ G: 弧形拨柄;
⑦ XX: 拨柄高度H: 3~15mm;
⑧ N: 方形外壳;
⑨ 1: 端子焊脚规格TYPE-1; 2: 端子焊脚规格TYPE-2;
3: 端子焊脚规格TYPE-3; 4: 端子焊脚规格TYPE-4;
5: 端子焊脚规格TYPE-5;
⑩ X: 拨柄颜色: B-黑色; W-白色; R-红色
⑪ X: 主体颜色: B-黑色; W-白色; R-红色

5.50 [0.217]

4.00 [0.157] Travel

3.30 [0.130]



产品凸码标识

XKB 3A 125/250VAC

8.50 [0.335]

2.00 [0.079]

4.50 [0.177]

9.00 [0.354]


0.50 [0.020]

4.00 [0.157]


XKB 3A 125/250VAC

SS Series
3A 125/250VAC

产品字码标识



CIRCUIT



ANGULAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	

XKB

DESIGN
CHECKED
APPROVED

桑 葚

VIEW:

UNIT: mm/in

SIZE: A4

MODEL TYPE:
SLIDE SWITCH

PART NO.:
SS-0312SG-XXN2BB
DWG NO.:

SCALE	PAGE	REVISION
N/A	1/1	A0