

1


2

3

4

| REVISIONS |         |          |                 |            |        |
|-----------|---------|----------|-----------------|------------|--------|
| REV.      | ECN NO. | LOCATION | DESCRIPTION     | DATE       | DESIGN |
| A0        | N/A     |          | INITIAL RELEASE | 2024.05.09 |        |
|           |         |          |                 |            |        |

16.20 [0.638]



10.50 [0.413]

## 规格 Specification:

1.额定值 Rating:3A 125/250VAC

2.接触电阻 Contact resistance:≤30 mΩ

3.绝缘电阻 Insulation resistance:≥100 MΩ(DC500V/Min)

4.电气寿命 Electronics life:&gt;10000 cycles

5.操作力 Operation force:500±150gf

6.所有材料符合Rohs要求 All materials are Rohs compliant

## PART NO.:

SS-X 03 12 S G-XX N 2 X X  
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪

① SS: 立式拨柄开关;

② X: A: 金属外壳;

BLANK: 塑胶外壳;

③ 03: 额定值3A;

④ 12: 单排两档;

⑤ S: 焊线端子;

⑥ G: 弧形拨柄;

⑦ XX: 拨柄高度H: 3~15mm;

⑧ N: 方形外壳;

⑨ 1: 端子焊脚规格TYPE-1; 2: 端子焊脚规格TYPE-2;

3: 端子焊脚规格TYPE-3; 4: 端子焊脚规格TYPE-4;

5: 端子焊脚规格TYPE-5;

⑩ X: 拨柄颜色: B-黑色; W-白色; R-红色

⑪ X: 主体颜色: B-黑色; W-白色; R-红色

A

A

B

B

C

C


D

D

5.50 [0.217]

4.00 [0.157] Travel

3.30 [0.130]



产品凸码标识

8.50 [0.335]

2.00 [0.079]

4.50 [0.177]

9.00 [0.354]


0.50 [0.020]

4.00 [0.157]


**XKB** **US**

SS Series  
3A 125/250VAC

产品字码标识



CIRCUIT



|                        |       |
|------------------------|-------|
| ANGULAR                | ±5°   |
| X.                     | ±0.40 |
| X.x                    | ±0.30 |
| X.xx                   | ±0.20 |
| X.xxx                  | ±0.15 |
| UNSPECIFIED TOLERANCES |       |

**XKB**

DESIGN

桑 葚

VIEW:

MODEL TYPE:  
SLIDE SWITCH

CHECKED

UNIT: mm/in

PART NO.:  
SS-0312SG-XXN2BB

APPROVED

SIZE: A4

DWG NO.:

XKB INDUSTRIAL PRECISION CO.,LIMITED

|       |      |          |
|-------|------|----------|
| SCALE | PAGE | REVISION |
| N/A   | 1/1  | A0       |

1

2

3

4