






RoHS

CAD GENERATED DRAWING. DON'T CHANGE BY HAND.

REV.	ECN. NO.	APPD.



Circuit Diagram



PCB Layout (Pattern side)

Specification

NO		
1	Contact rating	4V DC 300mA
2	Insulation resistance	≤100Ω
3	Operation Force	200±70gf
4	Travel	2.0±0.1mm
5	Contact resistance	>100MΩ
6	Dielectric Strength	250V 50Hz 1Min
7	Operating Life	10000

5	TERMINAL	4	PBS	Ag Plating
4	CASE	1	LCP	BLACK
3	CONTACT	1	Beryllium alloy	Ag Plating
2	COVER	1	SUS	Nature
1	KNOB	1	PA46	Black
NO.	PART NAME	Q' TY	MATERIAL	FINSH/COLOR

X.	±0.50	X.°	±2°
.X	±0.30	.X°	±1°
.XX	±0.10	.XX°	±0.5°
.XXX	±0.05		

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF YIYUAN TECHNOLOGY CO.,LTD AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF YIYUAN TECHNOLOGY CO.,LTD

UNITS	mm
MAT'L	
FINISH	
Q' TY	



深圳市怡远科技有限公司
SHENZHEN YIYUAN TECHNOLOGY CO., LTD

PART NO.
YSS18-23N02S2-G2


TITLE:
SLIDE SWITCH

APPD: ROGER

DWG NO.:

CHKD: ROC

DR: BILLY WANG 2020/08/21



SCALE	SHEET	REV.
1/1	1/1	A1