





A		B		C		D		E	
REV.	DESCRIPTION				ECN NO.	NAME	DATE		



SPECIFICATIONS

Current Rating: 3Amps
 Insulation Resistance: 1000MΩ Min
 Contact Resistance: 20MΩ Max
 Withstanding Voltage: AC 1000V
 Operation Temperature: -40° to +105°
 Contact Material: Copper Alloy
 Standard: PBT
 Insulator Material: Polyester(UL 94V-0)
 Contact Plating: Gold Flash
 Max.Processing Temp: 200°C for 30-60seconds
 (220°C for 5seconds)

P/N	PIN	DIM.A	DIM.B
A254UP-ZS1P	1	0.00	2.54
A254UP-ZS2P	2	2.54	5.08
A254UP-ZS3P	3	5.08	7.62
A254UP-ZS4P	4	7.62	10.16
A254UP-ZS5P	5	10.16	12.70
A254UP-ZS6P	6	12.70	15.24
A254UP-ZS7P	7	15.24	17.78
A254UP-ZS8P	8	17.78	20.32
A254UP-ZS9P	9	20.32	22.86
.....
A254UP-ZS40P	40	(PIN-1)X2.5 4	(PIN)X2.54



RECOMMEND P.C.B LAYOUT
 PCB TOLERANCE: ±0.05 (TOP VIEW)

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				
DIM.	TOL.	TITLE: 2.54PH H2.5 2xNP in 180度 PC3.0 PA6.0 PB2.5 L11.5 PBT				
X		DWG. NO.: A254UP-ZSNP		DRAWN: MAX		
X.X	±0.30	PART NO.: A254UP-ZSNP		CHECKED: ELLA		
X.XX	±0.25	UNIT: mm		APPROVED: WILL		
X.XXX	±0.15	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn	
GENERAL ANGLE:	±3°					