





REV.	ECN. NO.	APPD.




SCHEMATIC



P.C.B.LAYOUT (BOTTOM VIEW)

* CRITICAL DIMENSION

- ELECTRICAL CHARACTERISTICS
1. RATING: DC 30V 0.1A
 2. CONTACT RESISTANCE: 100mΩ MAX
 3. INSULATION RESISTANCE: 100MΩ MIN
 4. DIELECTRIC STRENGTH: AC 250V (50~60Hz) /60S
- MECHANICAL CHARACTERISTICS
1. PRACTICAL TEMPERATURE RANG: -40℃~+85℃
 2. OPERATING FORCE: 400±50gf
 3. MECHANICAL LIFE: 50,000 cycles

7	CAM STICK	1	SUS	NATURAL	X. ±0.50	X. ° ±2°	UNITS mm	 深圳市怡远科技有限公司 SHENZHEN YIYUAN TECHNOLOGY CO.,LTD	PART NO. YTS8513L400EB	TITLE: 规格书 8.5*13 物料号 2.8*2.8 物料			
6	TERMINAL	6	C2680R-EH	Ag COATING	. X ±0.30	. X ° ±1°							
5	CASE	1	PBT	GRAY	. XX ±0.10	. XX ° ±0.5°	MAT' L 						
4	CONTACT	2	C5210R-EH	Ag CLAD	. XXX ±0.05								
3	COVER	1	PPA	BLACK	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF YIYUAN TECHNOLOGY CO.,LTD AND SHALL NOT BE REPRODUCED. COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF YIYUAN TECHNOLOGY CO.,LTD			FINISH 	APPD: ROGER	DWG NO. : YTS8513L400EW			
2	SPRING	1	SUS	NATURAL									
1	KNOB	1	POM	WHITE									
NO.	PART NAME	Q' TY	MATERIAL	FINISH/COLOR				Q' TY 	CHKD: ROC				
										DR: BILLY WANG 2020/08/21			
													
									SCALE	SHEET	REV.		
								1/1	1/1	A1			