







- 材质要求:
- 1.频率: 0~3GHz
 - 2.阻抗: 50Ω
 - 3.VSWR: ≤1.15
 - 4.工作电压: 1000V
 - 5.耐压: 1000V
 - 6.绝缘电阻: ≥5000MΩ
 - 7.接触电阻: 内导体≤3mΩ; 外导体≤2mΩ
 - 8.环境温度: -65~+165℃ (PE CABLE-40~+85℃)
 - 9.机械寿命: 500次
 - 10.材质:
 - 外壳: 黄铜 镀金
 - 插针: 黄铜 镀金
 - 绝缘子: PTFE
 - 螺母: 黄铜 镀金
 - 花齿: 黄铜 镀金
 - 11.未注公差按±0.2

Ordering Information

XD - *** - *** - *H - D00* - 01

Series	Type	Height	Pin	Product No.
SMA直插式	3件套	6.5x6.5x16.5H	DP008-01	
SMA直插式	3件套	6.5x6.5x16.5H	DP008-01	
SMA直插式	3件套	6.5x6.5x16.5H	DP008-01	



GENERAL TOLERANCE		制图	01
DIM TOL		DRAWING	
X.X ±0.30		审核	
X.XX ±0.20		CHECK	
X.XXX ±0.10		批准	
Angle ±3.0°		APPROVAL	
		比例	
		SCALE	
		投影	
		Projection	

深圳讯答科技有限公司			
ShenzhenXunDaTechnology Co.,Ltd			
产品名称	SMA 直插 插孔 带脚偏	版本	A
TITLE	3件套 6.5x6.5x16.5H	REV.	
产品料号	XD-SMA-KE-16.5H-DP008-01	单位	mm
PART NO.		UNITS	
材料		页次	1/1
MATERIAL		SHEET	