






- 1.频率: 0~3GHz
- 2.阻抗: 50Ω
- 3.VSWR: ≤ 1.15
- 4.工作电压: 335V
- 5.耐压: 1000V
- 6.绝缘电阻: $\geq 5000\text{M}\Omega$
- 7.接触电阻: 内导体 $\leq 3\text{m}\Omega$; 外导体 $\leq 2\text{m}\Omega$
- 8.环境温度: $-65^{\circ}\text{C} \sim +165^{\circ}\text{C}$ (PE CABLE-40 $^{\circ}\text{C} \sim +85^{\circ}\text{C}$)
- 9.机械寿命: 500 次
- 10.材料:
 - 外壳: 黄铜 镀金
 - 插针: 黄铜 镀金
 - 绝缘子: PTFE
- 11.未注公差按 ± 0.2



XD - *** - *** - *H - D 00* - 01

Series SHA(散列式) SHA(流散式) MC(可擦式) MMC(可擦流散式)	Type 散列+流式 W=流式 J=散列 K=擦机 E=擦擦	High (高深)	On-Board DF=数据 DP=编程 DT=特殊	产品序号
---	---	--------------	-------------------------------------	------



GENERAL TOLERANCE	制图 DRAWING	01	 深圳讯答科技有限公司 ShenzhenXunDaTechnology Co.,Ltd			
DIM TOL	审核 CHECK		产品名称 TITLE	SMA 弯式 插孔 带脚 6x6x14.5H	版本 REV.	A
X.X ±0.30	批准 APPROVAL		产品料号 PART NO.	XD-SMA-KWE-14.5H-D002-01	单位 UNITS	mm
X.XX ±0.20	比例 SCALE		材料 MATERIAL		页次 SHEET	1/1
X.XXX ±0.10	投影 Projection					
Angle ±3.0°						