


Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)

SPECIFICATIONS

Rated Current:3.0AMP
Contact Resistance:20mΩ Max
Withstand Voltage:1000V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:-40°C to +105°C


Contact Material:Brass
Contact Plating:Au Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 10 seconds)



Dimension antitheses list				
ITEM	PA	PC	C	L
Standard	6.00	3.00	21.00	30.00
Alternate				

Ordering Information

PZ 254 - * - N - Z - C* - ** - DP				
No. of Rows 1=Single Row 2=Dual Row	No. of Pins 2=40Pin 3=60Pin 4=80Pin	Type (双排/单排)	Contact Plating G0:Gold Flash G1:10u" Gold G2:30u" Gold G3:50u" Gold G4:100u" Gold G5:150u" Gold G6:300u" Gold S0:Gold Flash/Tin S1:Tin	Dual Plastic (双排)



GENERAL TOLERANCE

制图
DRAWING

审核
CHECK

批准
APPROVAL

比例
SCALE

投影
Projection

材料
MATERIAL



深圳市华灿天禄电子有限公司
ShenzhenhuaciantianluELECTRONICS CO.,LTD

产品名称
TITLE

产品料号
PART NO.

材料
MATERIAL

版本
REV.

单位
UNITS

页次
SHEET

1/1