

A	Dept	晨翔焊线式D-SUB, 9P, 公头, 白色胶芯, 镀锡外壳, 半金锡端子 无螺丝				REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED	A
	Qty					A	NEW RELEASE	JLZ 09/18/24'			
	DC	晨翔料号: DS1033-09MWTSiSS									
	ED										
	IE										
B	ISO										B
	PD										
	R&D										
	SD										
	QA										
C	QC										C
	QE										
D											D
E											E
F											F
G											G
H											H

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION		TITLE
X.	±0.60	X.	±5°	UNITS	mm	D-SUB 焊线式
.X	±0.38	.X	±3°	SHEET SIZE	A4	SERIES DS1033 SERIES
.XX	±0.25	.XX	±2°	 晨翔电子有限公司 CONNFY CONNFY ELECTRONIC CO. LTD		
DRAWING TYPE		CUSTOMER				
SCALE		1:1	SHEET 1 OF 1			
DRAWING NO.		C-DS1033-XXXX-A				

备注:

1. 电性说明:

1.1 接触阻抗: 20毫欧最大

1.2 耐电压: 500伏交流电一分钟

1.3 绝缘阻抗: 1000兆欧最小

2. 环境特性:




2.1 工作温度: -40至105摄氏度



3. 材料:

3.1 胶芯: PBT, 白色

3.2 端子: H62黄铜, 半金锡

3.3 外壳: 铁料, 前壳镀锡, 后壳镀锡





GENERAL TOLERANCE		ANGLE TOLERANCE	
X.	±0.60	X.	±5°
.X	±0.38	.X	±3°
.XX	±0.25	.XX	±2°

DRAWING TYPE	CUSTOMER		
SCALE	1:1	SHEET	1 OF 1
DRAWING NO.	C-DS1033-XXXXX-A		

PROJECTION		TITLE	D-SUB 焊线式	
UNITS	mm			
SHEET SIZE	A4	SERIES	DS1033 SERIES	