


A	Dept	晨翔焊线式D-SUB, 9P, 公头, 蓝色胶芯, 镀锡外壳, 镀金端子 无螺丝				REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED	A
	Qty					A	NEW RELEASE	JLZ 09/18/24'			
	DC	晨翔料号: DS1033-09MUT8SS									
	ED										
	IE										
B	ISO										B
	PD										
	R&D										
	SD										
	QA										
C	QC										C
	QE										
D										D	
E										E	
F										F	
G										G	
H										H	

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION		TITLE
X.	±0.60	X.	±5°	UNITS	mm	D-SUB 焊线式
.X	±0.38	.X	±3°	SHEET SIZE	A4	SERIES DS1033 SERIES
.XX	±0.25	.XX	±2°	 晨翔电子有限公司 CONNFLY CONNFLY ELECTRONIC CO. LTD		
DRAWING TYPE		CUSTOMER				
SCALE	1:1	SHEET	1 OF 1			
DRAWING NO.		C-DS1033-XXXX-A				



备注:

1. 电性说明:

1.1 接触阻抗: 20毫欧最大

1.2 耐电压: 500伏交流电一分钟

1.3 绝缘阻抗: 1000兆欧最小

2. 环境特性:

2.1 工作温度: -40至105摄氏度

3. 材料:

3.1 胶芯: PBT, 蓝色

3.2 端子: H62黄铜, 镀金

3.3 外壳: 铁料, 前壳镀锡, 后壳镀锡

此图提供的信息来自宁波晨翔电子有限公司并且是保密的。禁止向收件人以外的任何一方披露信息。本文包含的知识产权及其权利(包括但不限于商标、专利、版权, 商业秘密和技术知识) 仅由晨翔或其附属公司拥有。未经晨翔事先书面同意, 严禁未经授权的复制或修改。晨翔可以自行决定强制执行其知识产权; 不履行或延迟行使这些权利并不构成对这些权利的放弃。