


Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)

SPECIFICATIONS

Rated Current:3.0AMP
Contact Resistance:20mΩ Max
Withstand Voltage:1000V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:-40°C to +105°C

Contact Material:Brass
Contact Plating:Au Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 10 seconds)



Dimension antitheses list				
ITEM	PA	PC	C	L
Standard	3.00	3.00	6.00	12.00
Alternate				

Ordering Information

PZ 254 - * - N - Z - C* - ** - DP

No. of Rows
1=Single Row
2=Dual Row

No. of Pins
2=40Pin
3=60Pin
4=80Pin

Type
(双排/单排)

Contact Plating
G0:Gold Flash
G1:1u" Gold
G2:3u" Gold
G3:5u" Gold
G4:10u" Gold
G5:15u" Gold
G6:30u" Gold
S0:Gold Flash/Tin
S1:Tin

Dual Plastic
(双塑)



GENERAL TOLERANCE	
DIM	TOL
X.X	±0.30
X.XX	±0.20
X.XXX	±0.10
Angle	±3.0°

制图 DRAWING
审核 CHECK
批准 APPROVAL
比例 SCALE
投影 Projection



深圳市华灿天禄电子有限公司 ShenzhenhuaciantianluELECTRONICS CO.,LTD			
产品名称 TITLE	2.54 双排 直排针 双塑	版本 REV.	A
产品料号 PART NO.	PZ254-2-N-Z-C6-XX-DP(PA.3.0)	单位 UNITS	mm
材料 MATERIAL		页次 SHEET	1/1